



ADA910T

RCBO 1P+N 6kA C-10A 30mA A Class

Technical properties

Architecture

| | |
|---------------------------|-------|
| Neutral position | right |
| Number of protected poles | 1 |
| Number of poles | 2 P |
| Type of pole | 1P+N |
| Curve | C |

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Connectivity

| | |
|---|------------------|
| Top connection alignment for modular devices | Aligned terminal |
| Bottom connection alignment for modular devices | Aligned terminal |

Main electrical features

| | |
|------------------------------|--------------|
| Rated operational voltage Ue | 230 - 240 V~ |
| Type of supply voltage | AC |

Voltage

| | |
|--|-------|
| Dielectric strength value of power frequency | 2 kV |
| Rated insulation voltage | 500 V |
| Max operating voltage | 240 V |
| Rated impulse withstand voltage | 4 kV |

Electric current

| | |
|--|----------------|
| Rated residual operating current | 30 mA |
| Rated current | 10 A |
| Withstand not tripping on 8-20 μ s wave | 250 A |
| Breaking and opening capacity | 4500 A |
| min/maxi threshold value of the AC thermal operation | 1.13 / 1.45 In |
| Magnetic regulating current | 5 / 10 In |

Electric current / temperature

| | |
|----------------------|--------|
| Rating current -25°C | 12 A |
| Rating current -20°C | 11.8 A |
| Rating current -15°C | 11.7 A |
| Rating current -10°C | 11.5 A |
| Rating current -5°C | 11.3 A |

| | |
|---------------------|--------|
| Rating current 0°C | 11.1 A |
| Rating current 5°C | 11 A |
| Rating current 10°C | 10.8 A |
| Rating current 15°C | 10.6 A |
| Rating current 20°C | 10.4 A |
| Rating current 25°C | 10.2 A |
| Rating current 30°C | 10 A |
| Rating current 35°C | 9.9 A |
| Rating current 40°C | 9.7 A |
| Rating current 45°C | 9.6 A |
| Rating current 50°C | 9.4 A |
| Rating current 55°C | 9.3 A |
| Rating current 60°C | 9.1 A |
| Rating current 70°C | 6.8 A |

Current correction factors

| | |
|---|------|
| Correction factor of rating current for 2 devices placed side-by-side | 1 |
| Correction factor of rating current for 3 devices placed side-by-side | 0.95 |
| Correction factor of rating current for 4 and 5 devices placed side-by-side | 0.9 |
| Correction factor of rating current for 6 devices placed side-by-side | 0.85 |

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 68 mm |
| Height of installed product | 83 mm |
| Width of installed product | 35 mm |

Frequency

| | |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 3.4 W |
| Power loss per pole at In | 2.8 W |

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 2000 |
| Number of mechanical operations | 2000 |

Installation, mounting

| | |
|---|--------------------|
| Type of top connection for modular devices | with screw |
| Tightening torque | 2,1Nm |
| Type of top rail clip for modular devices | NA |
| Type of bottom rail clip for modular devices | plastic |
| Type of Bottom Connection for modular devices | Blconnect + bypass |
| Top removability for modular devices | No |
| Bottom removability for modular devices | Yes |
| Suitable for flush-mounting | Yes |

Subject to technical modifications

Connection

| | |
|--|------------------------|
| Connection cross-section at output with screw, for flexible conductor | 1 / 16 mm ² |
| Connection cross-section at output with screw, for massive conductor | 1 / 25 mm ² |
| Connection cross-section for rigid conductor, upstream terminals with screws | 1 / 25 mm ² |
| Connection cross-section of the access with screws, with flexible conductor | 1 / 16 mm ² |
| Cage clamp position | in line |
| Downstream cage clamp delivery status | opened |
| Upstream cage clamp delivery status | opened |
| Connection cross-section of input and output with screws, for massive conductors | 1 / 25 mm ² |
| Connection cross section of access and exit with screws, for flexible conductor | 1 / 16 mm ² |

Cable

| | |
|---|---------------------|
| Length of conductors used for the heating test (m) according to product standard | 1 m |
| Conductor cross-section used for heating test(mm ²) according to product standard | 1.5 mm ² |

Equipment

| | |
|---------------------------------------|-----|
| Can be accessorized | Yes |
| With transparent product label holder | Yes |

Standards

| | |
|---------------|------------------------------|
| Standard text | IEC 61009-1 ; AS/NZS 61009-1 |
|---------------|------------------------------|

Safety

| | |
|-----------------------|-----|
| Residual current type | A |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |

Use conditions

| | |
|--|------------------|
| Operating temperature | -25...40 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Altitude | 2000 m |
| Air humidity protection | for all climates |
| Storage/transport temperature | -25...70 °C |

temperatur

| | |
|---|---------|
| Temperature of calibration | 30 °C |
| Ambient air temperature during heating test according to the product standard | 23.8 °C |
| Max. admissible temperature on accessible parts (intended to be touched) | 53.2 °C |
| Max. admissible temperature on accessible parts (manual operating means) | 42.7 °C |

| | |
|--|---------|
| Max. admissible temperature on access. parts (not touched for normal operation) | 67 °C |
| Max. admissible temperature on terminals | 58.7 °C |
| Temp.-rise limits for access. parts (toggle) according to product standard | 25 K |
| Temp.-rise limits for access. parts (not touched) according to product standard | 60 K |
| Temp.rise limits for access. parts (to be touched) according to product standard | 40 K |
| Temperature-rise limits for terminals according to the product standard | 65 K |
| Temperature-rise measured on accessible parts at In (manual operating means) | 2.7 K |
| Temperature-rise measured on access. parts at In (not touched normal operation) | 27 K |
| Temperature-rise measured on accessible parts at In (intended to be touched) | 13.2 K |
| Temperature-rise measured on terminals at In | 18.7 K |