



WMSS82N

**2 Gang Double Pole Switched Socket Dual Earth with LED Indicators**

**Technical characteristics**

**Functions**

Overvoltage protection No

**Configuration**

Number of modules 0

**Main electrical features**

Nominal voltage 250 V AC

Rated current 13 A

**Electric current**

Rated current 13 A

**Dimensions**

Depth 29.5 mm

Height 86 mm

Width 146 mm

**Cover, door**

Cover Full cover plate

**Power supply**

Special power supply No special power supply

**Materials**

Colour white

Type of surface treatment untreated

**Installation, mounting**

Fixing type With screws

Installation mode for flush-mounted and hollow-wall mounting ; for screw fastening

**Connection**

Type of connection screw

**Cable**

Wiring with double earth connection

**Scope of delivery**

Component with 2 fixing screws M3.5 x 30 mm

**Equipment**

**Safety**

---

IK protection code against mechanical impacts

sonstige

Protection

Enhanced contact protection