



ADA940T

**RCBO 1P+N 6kA C-40A 30mA A Class**

**Technical properties**

**Architecture**

Type of pole	1P+N
Curve	C

**Electric current**

Rated current	40 A
Rated residual operating current $I_{\Delta n}$	30 mA
Rated current -25°C	46,90 A
Rated current at -20°C	46,30 A
Rated current -15°C	45,60 A
Rated current -10°C	45 A
Rated current -5°C	44,40 A
Rated current at 0°C	43,80 A
Rated current 5°C	43,10 A
Rated current 10°C	42,50 A
Rated current 15°C	41,90 A
Rated current at 20°C	41,30 A
Rated current 25°C	40,60 A
Rated current 30°C	40 A
Rated current 35°C	39,40 A
Rated current at 40°C	38,80 A
Rated current at 50°C	37,50 A
Rated current 55°C	36,90 A
Rated current 60°C	36,20 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0,95
Correction factor of rating current for 4 and 5 devices placed side by side	0,90
Correction factor of rating current for 6 devices placed side by side	0,85
Min./max. threshold value of the AC thermal operation	1,13 - 1,45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP2X

**Main electrical attributes**

## Connectivity

Type of connection	Screw terminal
--------------------	----------------

## Voltage

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	240 V
Rated operational voltage U <sub>e</sub>	230 - 240 V
Overvoltage category according to IEC 60947-1	3

## Power

Total power loss under I <sub>N</sub>	11,10 W
---------------------------------------	---------

## Frequency

Frequency	50 - 50 Hz
-----------	------------

## Use conditions

Max. Altitude	2000 m
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

## Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

## Connection

Cross-section flexible conductor	1 - 16 mm <sup>2</sup>
Cross-section rigid conductor	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 25 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 25 mm <sup>2</sup>

## Installation, mounting

Nominal tightening torque	2,10 - 2,10 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect, Bypass

## Capacity

Number of modules	2
-------------------	---

## Dimensions

Height	83 mm
--------	-------

Width	35 mm
Depth	68 mm
<b>Compatibility</b>	
Suitable for DIN Rail	Yes