



WRPS16BSW

Intermediate Switch Brushed Steel White Insert

Technical characteristics

Configuration

Switch mode	intermediate
-------------	--------------

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Frequency	50/60 Hz
Rated current	20 A

Dimensions

Depth	24 mm
Insertion depth	11.2 mm
Height	86 mm
Width	86 mm

Materials

Material	stainless steel
----------	-----------------

Connection

Conductor cross-section	2 x 4 mm ²
-------------------------	-----------------------

Equipment

Lighting	without lighting (cannot be illuminated)
----------	--

Use conditions

Insert	insert white
--------	--------------

Identification

Appliance switch type	No
-----------------------	----