



EC051

Single phase KWHmeter direct 32A 1M with pulsed output

Technical properties

Architecture

Type of pole 1P+N

Functions

Precision class B

Tarif type One-tariff

Configuration

Number of modules 1

Compatibility

Suitable for Purchase

Main electrical features

Rated operational voltage Ue 185 / 230 / 275 V

Frequency 50 Hz

Voltage

Rated insulation voltage 4 kV

Electric current

Operating current 0.02 / 32 A

Rated current 32 A

Max. measurement circuit current 32 A

Dimensions

Width of installed product 17.5 mm

Power

Power consumed 6.7 VA

Total power loss under IN 6.7 W

Plage Impulsion/KWh 10 Imp/kWh

Electrical specifications

Type of pulse generator électrical

Measurement

Idle power measurement activ energy

Voltage measurement range 230 V

Type of measuring instrument electronical

Principle of measurement Direct measurement

Power supply

Number of phases for the power supply	1-phase
---------------------------------------	---------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
---	----------------------

Type of Bus connexion	other
-----------------------	-------

Connection	direct connection
------------	-------------------

Settings

Value of a pulse	100 Wh
------------------	--------

Equipment

Number of positions total	6
---------------------------	---

Tariff model of kilowatt-hour meter	Externa
-------------------------------------	---------

Rolling code	No
--------------	----

Use

Pulse duration	100 ms
----------------	--------

Interval between 2 pulses	48000 ms
---------------------------	----------

Standards

Approval	MID (Measuring Instruments Directive)
----------	---------------------------------------

Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------

Storage/transport temperature	-25...70 °C
-------------------------------	-------------