



ADM420T

## RCBO 4P 6kA C-20A 30mA A

### Technical properties

#### Electric current

Rated current	20 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	23,80 A
Rated current at -20°C	23,50 A
Rated current -15°C	23,20 A
Rated current -10°C	22,90 A
Rated current -5°C	22,50 A
Rated current at 0°C	22,20 A
Rated current 5°C	21,80 A
Rated current 10°C	21,50 A
Rated current 15°C	21,10 A
Rated current at 20°C	20,80 A
Rated current 25°C	20,40 A
Rated current 30°C	20 A
Rated current 35°C	19,60 A
Rated current at 40°C	19,10 A
Rated current at 45°C	18,60 A
Rated current at 50°C	18,20 A
Rated current 55°C	17,70 A
Rated current 60°C	17,20 A

#### Architecture

Curve	C
Neutral position	Right
Type of pole	4P
Number of protected poles	4

#### Capacity

Number of modules	4
-------------------	---

#### Safety

Residual current type	A
Ingress Protection (IP) class	IP2X

#### Voltage

Type voltage supply	AC
Rated operational voltage U <sub>e</sub>	230 - 415 V
Rated insulation voltage U <sub>i</sub>	500 V

Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage Uimp	4000 V
Overvoltage category according to IEC 60947-1	3
<b>Main electrical attributes</b>	
Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm
<b>Frequency</b>	
Frequency	50 - 50 Hz
<b>Connection</b>	
Cross-section of input with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 25 mm <sup>2</sup>
<b>Installation, mounting</b>	
Nominal tightening torque	2 - 2 Nm
360° mounting position possible	Yes
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect, Bypass
<b>Use conditions</b>	
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 40 °C
<b>Dimensions</b>	
Height	84 mm
Width	71 mm
Depth	70 mm
<b>Power</b>	
Total power loss under IN	11,70 W