



ECR180T

## 1 Phase kWhmeter direct 3x80A 4M MODBUS

### Technical properties

#### Architecture

Bus system	MODBUS
Number of poles	2 P
Fixing mode	DIN rail type O (symmetrical)

#### Functions

Tarif type	T1...T2 (230V AC) / T1...T4 Modbus
------------	------------------------------------

#### Configuration

Number of modules	4
-------------------	---

#### Compatibility

Suitable for	Purchase / supply
--------------	-------------------

#### Main electrical features

Rated operational voltage Ue	92 / 276 V
Type of supply voltage	AC
Frequency	50 Hz

#### Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

#### Electric current

Minimum operating current	0.015 A
Operating current	0.015 / 80 A
Rated current	80 A
Reference current	5 A
Max. measurement circuit current	80 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	72 mm

#### Power

Power consumed	2 VA
Total power loss under IN	1 W

#### Electrical specifications

Type of pulse generator	optical
-------------------------	---------

**Measurement**

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electrical
Principle of measurement	Direct measurement

**Installation, mounting**

Tightening torque	2Nm
Mounting type	din-Rail

**Connection**

Wire cross section of metering entrance wire	33 mm <sup>2</sup>
Wire cross section of metering outgoing wire	33 mm <sup>2</sup>

**Equipment**

Type of display	retro illuminated display
Tariff model of kilowatt-hour meter	Externa
Type of counter	three-point system

**Standards**

Standard text	IEC 62053-21 / 23 ; IEC 61557-12
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
Protection class	isol.class II

**Use conditions**

Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...70 °C