



ECR380D

### 3 Phase kWhmeter direct 80A 4M MODBUS MID

#### Technical properties

##### Architecture

Bus system	MODBUS
Type of pole	3P+N

##### Electric current

Rated current	80 A
Maximum measuring circuit current	80 A

##### Capacity

Number of modules	4
-------------------	---

##### Connectivity

Type of connection	Direct connection
Connectivity type	ModBus RS-485 3 wires

##### Dimensions

Height	92 mm
Width	72 mm
Depth	60 mm

##### Main electrical attributes

Type of pulse generator	Optical
-------------------------	---------

##### Compatibility

Suitable for	Purchase/supply
--------------	-----------------

##### Connection

Cross-section of metering input	33 - 33 mm <sup>2</sup>
Cross-section of metering output	33 - 33 mm <sup>2</sup>
Connector/plug type Bus system	Bus connection terminal

##### Installation, mounting

Nominal tightening torque	2 - 2 Nm
---------------------------	----------

##### Mechanical features

Nominal tightening torque digital terminal	0,50 - 0,50 Nm
--	----------------

##### Measurement

Measuring system	Direct measurement
Type of measuring instrument	Electronic
Current measurement range	0,25 - 80,0 A

Measurement range voltage Ph-N	92 - 276 V
Measurement range voltage Ph-Ph	160 - 480 V
Frequency measuring range	45 - 65 Hz

#### Functions

Accuracy class	B
Tariff type	T1...T2 (230V AC)/T1...T8 Modbus
Is calibrated	Yes

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Use conditions

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

#### Power

Power consumption VA	2 VA
Total power loss under IN	0,60 W