



ECR310D



### 3 Phase kWhmeter direct 125A 6M MODBUS MID

#### Technical properties

##### Architecture

Bus system	MODBUS
Number of poles	4 P
Type of pole	3P+N

##### Functions

Precision class	B
Tarif type	T1...T2 (230V AC) / T1...T8 Modbus

##### Configuration

Number of modules	6
-------------------	---

##### Compatibility

Suitable for	Purchase / supply
--------------	-------------------

##### Main electrical features

Rated operational voltage Ue	92 / 480 V
Type of supply voltage	AC
Frequency	50 Hz

##### Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

##### Electric current

Minimum operating current	0.02 A
Operating current	0.02 / 125 A
Rated current	125 A
Reference current	5 A
Max. measurement circuit current	125 A

##### Dimensions

Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	107 mm

##### Power

Power consumed	2 VA
Total power loss under IN	0.6 W

##### Electrical specifications

Type of pulse generator

optical

### Measurement

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electrical
Principle of measurement	Direct measurement

### Power supply

Supply voltage	400 V $\pm$ 20%
----------------	-----------------

### Installation, mounting

Tightening torque	5Nm
Mounting type	din-Rail

### Connection

Wire cross section of metering entrance wire	50 mm <sup>2</sup>
Wire cross section of metering outgoing wire	50 mm <sup>2</sup>

### Equipment

Type of display	retro illuminated display
Tariff model of kilowatt-hour meter	Externa
Type of counter	4 wires counter

### Standards

Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
Certified product	MID (Measuring Instruments Directive)

### Safety

Protection class	isol.class II
Halogen free	No

### Use conditions

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-25...70 °C