



EE860



IP55

Motion detector comfort 220°, IP55, wall mounted, blanc

Technical properties

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Recommended installation height 2.5 m

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 220 °

Detection angle 220 °

Frontal detecting distance 16 m

Side detecting distance 10 m

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Lighting control

Response brightness, adjustable ≈ 5...1000 lx

Brightness measurement range 5 / 1000 Lux

Connection

Type of connection with screw terminals

Settings

Response value sensitivity adjustable Yes

Delay time, adjustable 5 s...30 mn

Scope of delivery

Component with fitting material

Equipment

Remote controllable EE806

Angle of horizontal detection 220 °

Slewing

vertically slewing and horizontally rotating

Safety

Protection index IP

IP55

Use conditions

Operating temperature

-20...55 °C

Storage/transport temperature

-20...60 °C

Identification

Application, usage

Motion detector

Main design line

Motion detectors