



EE861

Motion detector comfort 220° anthracite

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Height of installed product	2.5 m
Recommended installation height	2.5 m

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Detection

Detection angle	220 °
Detection angle	220 °
Frontal detecting distance	16 m
Side detecting distance	10 m

Materials

Colour	charcoal
Material	plastic

Lighting control

Response brightness, adjustable	≈ 5...1000 lx
Brightness measurement range	5 / 1000 Lux

Connection

Type of connection	with screw terminals
--------------------	----------------------

Settings

Response value sensitivity adjustable	Yes
Delay time, adjustable	5 s...30 mn

Scope of delivery

Component	with fitting material
-----------	-----------------------

Equipment

Remote controllable	EE806
Angle of horizontal detection	220 °
Slewing	vertically slewing and horizontally rotating

Safety

Protection index IP

IP55

Use conditions

Operating temperature

-20...55 °C

Storage/transport temperature

-20...60 °C

Identification

Application, usage

Motion detector

Main design line

Motion detectors