




EE811



IP41



Presence detector 360°, 2 channels, flush mounted, white

Technical properties

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50 Hz

Dimensions

Width of installed product	100 mm
Recommended installation height	2.5...3.5 m

Measurement

Detection Method	Passive Infrared
------------------	------------------

Power supply

Supply voltage	230 V
----------------	-------

Detection

Detection angle	360 °
Detection angle	360 °
Detection field Ø, on floor	≈ 12 m
Detection field Ø, at desk height	≈ 5 m
Frontal detecting distance	7 m
Side detecting distance	13 m

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	plastic

Lighting control

Response brightness, adjustable	≈ 5...1200 lx
Brightness measurement range	5 / 1200 Lux

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Settings

Response value sensitivity adjustable	Yes
Delay time, adjustable	≈ 1...30 mn

Equipment

Angle of horizontal detection	360 °
Slewing	Detector head slewing by 90°

Safety	
Protection index IP	IP41
Protection class	isol.class II
Use conditions	
Operating temperature	0...45 °C
Storage/transport temperature	-10...60 °C
Identification	
Application, usage	Motion detector
Main design line	Motion detectors