



EE812

μ IP41

**Presence detector 360°, 1/10V, flush mounted, white**

**Technical properties**

**Architecture**

Bus system Without

**Main electrical features**

Rated operational voltage Ue 230 V

Frequency 50 Hz

**Dimensions**

Height of installed product 31 mm

Width of installed product 100 mm

**Reach distance**

Max. transmission range 12m

**Power supply**

Supply voltage 230 V

**Detection**

Detection angle 360 °

Frontal detecting distance 7 m

Side detecting distance 13 m

**Materials**

Colour pure white

RAL colour RAL 9010 - Pure white

Material plastic

**Lighting control**

Brightness measurement range 5 / 1200 Lux

**Installation, mounting**

Maximum Mounting Height 4 m

**Settings**

Response value sensitivity adjustable Yes

**Equipment**

Angle of horizontal detection 360 °

**Safety**

Protection class isol.class II

**Use conditions**

---

Operating temperature	0...45 °C
Storage/transport temperature	-10...60 °C

---