



EG103E



## Digital time switch weekly 1 channel Evolution

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	1
Function	Presence simulation

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

Indication / display	LC display with illumination
----------------------	------------------------------

#### Main electrical features

Rated operational voltage U <sub>e</sub>	195 / 230 / 264 V
Frequency	50 Hz

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Length	85 mm
Width of installed product	35 mm
Width of rail mounted device (RMD)	2 modules

#### Power

Power consumed	6 VA
Total power loss under IN	2 W
Loss power at full load	≈ 2 W
Power dissipation per coil	0.5 W

#### Battery

Power reserve [years]	≈ 5 a
-----------------------	-------

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
230 V incandescent lamps and halogen lamps	max. 2300 W

#### Installation, mounting

Installation mode	for mounting on DIN rail
-------------------	--------------------------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Conductor cross-section (flexible)	1...6 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...10 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Type of connection	with screw

#### Settings

Number of program steps	56
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Program cycles	Programme cycles: 1 x 7 days
Programming cycle	1X7D.
Programs	holiday programme with date activation
Time	with automatic summer/winter time change-over

#### Equipment

Number of channels	1
Number of switching times for on/off	56
Supply failure reserve	5 years
With holidays program	Yes

#### Use

Cycle	weekly
-------	--------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-5...45 °C
Working accuracy	1,5
Storage/transport temperature	-20...70 °C