




EG203E



**IP20**

## Digital time switch weekly cycle 2 channels EVOLUTION

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	2
-----------------------------	---

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

Indication / display	LC display with illumination
----------------------	------------------------------

#### Main electrical features

Rated operational voltage Ue	195 / 230 / 265 V
Frequency	50 Hz

#### Voltage

Operating voltage	230 V~
-------------------	--------

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Length	85 mm
Width of installed product	35 mm
Width of rail mounted device (RMD)	2 modules

#### Power

Power consumed	6 VA
Total power loss under IN	4 W
Loss power at full load	≈ 4 W
Power dissipation per coil	0.5 W

#### Measurement

Running accuracy	± 1.5 s/day
------------------	-------------

#### Battery

Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

230 V incandescent lamps and halogen  
lamps

max. 2300 W

### Installation, mounting

Installation mode for mounting on DIN rail

### Connection

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Conductor cross-section (flexible)	1...16 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...10 mm <sup>2</sup>
Number of contacts	2
Type of connection	with screw terminals

### Settings

Number of program steps	56
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Program cycles	Programme cycles: 2 x 7 days
Programming cycle	2X7D.
Programs	holiday programme with date activation

### Equipment

Number of channels	2
Number of switching times for on/off	56
Supply failure reserve	5 years
With holidays program	Yes

### Use

Cycle	weekly
-------	--------

### Safety

Protection index IP	IP20
---------------------	------

### Use conditions

Operating temperature	-5...45 °C
Working accuracy	1,5
Storage/transport temperature	-20...70 °C