



EH011



## Daily time switch 1 channel, 1 modules with reserve

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	1
Switching cycles	min. 30000
Power reserve	≈ 200 h

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	210 / 230 V
Frequency	50 Hz

#### Voltage

Operating voltage	230 V~
-------------------	--------

#### Electric current

Max. power with $\cos \phi$ 0.6	3 A
Switching current at $\cos \phi = 0.6$	max. 3 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	80 mm
Width of installed product	18 mm
Width of rail mounted device (RMD)	1 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

#### Battery

Charging time of the power reserve in hours	120
---	-----

#### Fluorescent bulbs control

Compact fluorescent lamps	max. 100 W
---------------------------	------------

**Incandescent bulbs control**

Max. power with incandescent lamps	900 W
------------------------------------	-------

230 V incandescent lamps and halogen lamps	max. 900 W
--	------------

**Installation, mounting**

Mounting type	din-Rail
---------------	----------

Installation mode	for mounting on DIN rail
-------------------	--------------------------

**Connection**

Conductor cross-section (flexible)	1...6 mm <sup>2</sup>
------------------------------------	-----------------------

Conductor cross-section (rigid)	1.5...10 mm <sup>2</sup>
---------------------------------	--------------------------

Number of contacts	1
--------------------	---

Type of contacts	1 changeover
------------------	--------------

Type of connection	with screw terminals
--------------------	----------------------

**Settings**

Number of program steps	96
-------------------------	----

Summer / Winter time change	manual
-----------------------------	--------

Shortest switching time	15 mn
-------------------------	-------

Type of programming	analog
---------------------	--------

Program cycles	Programme cycle: 24 hours
----------------	---------------------------

Programming cycle	24H
-------------------	-----

Astro program	No
---------------	----

**Equipment**

Number of channels	1
--------------------	---

Number of switching times for on/off	96
--------------------------------------	----

Supply failure reserve	200 h
------------------------	-------

Switching cycles at $\cos \varphi = 0,6$	min. 30000
--	------------

**Use**

Cycle	daily
-------	-------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-10...55 °C
-----------------------	-------------

Working accuracy	1
------------------	---

Storage/transport temperature	-10...55 °C
-------------------------------	-------------