



EH111



## Time switch daily cycle with reserve 3 modules

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	1
Switching cycles	min. 50000
Power reserve	≈ 200 h

#### Configuration

Switch mode	change-over contact, usable as NC or NO
Number of modules	3

#### Main electrical features

Rated operational voltage $U_e$	230 V
Frequency	50 Hz

#### Voltage

Operating voltage	230 V~
-------------------	--------

#### Electric current

Max. power with $\cos \phi$ 0.6	3 A
Switching current at $\cos \phi = 0.6$	max. 3 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	54 mm
Width of rail mounted device (RMD)	3 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

#### Measurement

Running accuracy	± 1 s/day
------------------	-----------

#### Battery

Charging time of the power reserve in hours	120
---------------------------------------------	-----

**Fluorescent bulbs control**

Compact fluorescent lamps	max. 200 W
---------------------------	------------

**Incandescent bulbs control**

Max. power with incandescent lamps	900 W
------------------------------------	-------

230 V incandescent lamps and halogen lamps	max. 900 W
--------------------------------------------	------------

**Installation, mounting**

Mounting type	surface-mounted
---------------	-----------------

Installation mode	for mounting on DIN rail
-------------------	--------------------------

**Connection**

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
-------------------------------------------	----------------------

Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
------------------------------------	----------------------

Conductor cross-section (flexible)	1...4 mm <sup>2</sup>
------------------------------------	-----------------------

Conductor cross-section (rigid)	1...4 mm <sup>2</sup>
---------------------------------	-----------------------

Number of contacts	1
--------------------	---

Type of contacts	1 changeover
------------------	--------------

Type of connection	with screw terminals
--------------------	----------------------

**Settings**

Number of program steps	96
-------------------------	----

Summer / Winter time change	manual
-----------------------------	--------

Shortest switching time	15 mn
-------------------------	-------

Type of programming	analog
---------------------	--------

Program cycles	Programme cycle: 24 hours
----------------	---------------------------

Programming cycle	24H
-------------------	-----

Astro program	No
---------------	----

**Equipment**

Number of channels	1
--------------------	---

Number of switching times for on/off	96
--------------------------------------	----

Supply failure reserve	200 h
------------------------	-------

Switching cycles at $\cos \varphi = 0,6$	min. 20000
------------------------------------------	------------

**Use**

Cycle	daily
-------	-------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-10...45 °C
-----------------------	-------------

Working accuracy	1
------------------	---

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

Main design line	Light control
------------------	---------------