



ESC125

**Contactor 25A, 1NO, 230V~50/60Hz**

**Technical properties**

**Architecture**

Number of poles	1 P
-----------------	-----

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 V
------------------------------	-------

Frequency	50 Hz
-----------	-------

**Voltage**

Rated insulation voltage	250 V
--------------------------	-------

DC control voltage	0 V
--------------------	-----

Command voltage AC	230 V
--------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

**Electric current**

Rated current	25 A
---------------	------

Thermal rated current outside of housings	25 A
---	------

Acceptable current load with AC7 category A	25 A
---	------

Acceptable current load with AC7 category B	8.5 A
---	-------

**Dimensions**

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.85 mm
----------------------------	----------

**Power**

Inrush power absorbed	7.4 W
-----------------------	-------

Operating consumption	1.8 W
-----------------------	-------

Total power loss under IN	2.1 W
---------------------------	-------

Power loss per contact	1.5 W
------------------------	-------

Power dissipation per coil	0.6 W
----------------------------	-------

Contact rating with 230 V in AC7 category A	4.6 kW
---	--------

Contact rating with 230 V in AC7 category B	880 W
---	-------

**Tripping**

Time of response when opening	15 ms
-------------------------------	-------

Time of response when closing	25 ms
-------------------------------	-------

**Resistance**

---

Winding resistance	5500 $\Omega$
--------------------	---------------

---

**Endurance**

---

Electric endurance in number of cycles	30000
--	-------

---

Number of mechanical operations	1000000
---------------------------------	---------

---

**Fluorescent bulbs control**

---

Max. power with fluorescent parallel lamps	500 VA
--	--------

---

Fluorescent lamps in duo circuit	990 VA
----------------------------------	--------

---

Max. load fluorescent lamp	490 VA
----------------------------	--------

---

**Incandescent bulbs control**

---

Max. power with incandescent lamps	1100 W
------------------------------------	--------

---

**Connection**

---

Number of contacts	1
--------------------	---

---

Type of contacts	1NO
------------------	-----

---

Connection cross-section of the control cable solid	1 / 10 mm <sup>2</sup>
---	------------------------

---

**Equipment**

---

Can be accessorized	Yes
---------------------	-----

---

**Use**

---

Local operation/hand operation	No
--------------------------------	----

---

**Standards**

---

European directive WEEE	not concerned
-------------------------	---------------

---

**Safety**

---

Protection index IP	IP2X
---------------------	------

---

Protection class	isol.class II
------------------	---------------

---

**Use conditions**

---

Operating temperature	-10...50 °C
-----------------------	-------------

---

Storage/transport temperature	-40...80 °C
-------------------------------	-------------

---