



ESC226

## Contactors 25A, 2NC, 230V~50Hz

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

#### Electric current

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

#### Power

Inrush power absorbed	10.7 VA
Operating consumption	2.9 VA
Total power loss under IN	3 W
Power loss per contact	1.5 W
Power dissipation per coil	1 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

#### Tripping

Time of response when opening	15 ms
Time of response when closing	25 ms

#### Endurance

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations 100000

---

**Fluorescent bulbs control**

Max. power with fluorescent parallel lamps 810 VA

Fluorescent lamps in duo circuit 1990 VA

Max. load fluorescent lamp 950 VA

---

**Incandescent bulbs control**

Max. power with incandescent lamps 1900 W

---

**Connection**

Connection cross-section of the control cable solid 1 / 10 mm<sup>2</sup>

---

**Equipment**

Can be accessorized Yes

---

**Use**

Local operation/hand operation No

---

**Standards**

European directive WEEE concerned

---

**Safety**

Protection index IP IP2X

---

**Use conditions**

Operating temperature -10...50 °C

Storage/transport temperature -40...80 °C