



ESC125

**Contactor 25A, 1NO, 230V~50/60Hz**

**Technical properties**

**Architecture**

Number of poles	1 P
-----------------	-----

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage U <sub>e</sub>	230 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

**Dimensions**

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

**Power**

Inrush power absorbed	7.4 W
Operating consumption	1.8 W
Total power loss under I <sub>N</sub>	2.1 W
Power loss per contact	1.5 W
Power dissipation per coil	0.6 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

**Tripping**

Time of response when opening	15 ms
Time of response when closing	25 ms

<b>Resistance</b>	
Winding resistance	5500 Ω
<b>Endurance</b>	
Electric endurance in number of cycles	30000
Number of mechanical operations	1000000
<b>Fluorescent bulbs control</b>	
Max. power with fluorescent parallel lamps	500 VA
Fluorescent lamps in duo circuit	990 VA
Max. load fluorescent lamp	490 VA
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	1100 W
<b>Connection</b>	
Number of contacts	1
Type of contacts	1NO
Connection cross-section of the control cable solid	1 / 10 mm <sup>2</sup>
<b>Equipment</b>	
Can be accessorized	Yes
<b>Use</b>	
Local operation/hand operation	No
<b>Standards</b>	
European directive WEEE	not concerned
<b>Safety</b>	
Protection index IP	IP2X
Protection class	isol.class II
<b>Use conditions</b>	
Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C