



ESC263

Contactor 63A, 2NO, 230V~50Hz

Technical properties

Connection

Type of contacts	2NO
Number of contacts	2
Cross-section flexible conductor	1.5 - 16 mm ²
Cross-section rigid conductor	1.5 - 25 mm ²

Electric current

Rated current	63 A
---------------	------

Capacity

Number of modules	3
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	4000 V
Rated insulation voltage U _i	440 V
Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

Endurance

Number of mechanical operations	100000
Electric endurance in number of cycles	30000

Power

Total power loss under I _N	11,50 W
Inrush power absorbed	62,50 VA

Dimensions

Height	85 mm
Width	54 mm
Depth	60 mm

Equipment

Number of NO contacts	2
Number of NC contacts	0

