



ETC225

## Night & Day Contactor 25A, 2NO, 230V~50Hz

### Technical properties

#### Architecture

Type of order	Day Night
---------------	-----------

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 V
---------------------------------	-------

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	250 V
--------------------------	-------

DC control voltage	0 V
--------------------	-----

Command voltage AC	230 V
--------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

#### Electric current

Rated current	25 A
---------------	------

Thermal rated current outside of housings	25 A
---	------

Acceptable current load with AC7 category A	25 A
---	------

Acceptable current load with AC7 category B	8.5 A
---	-------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.85 mm
----------------------------	----------

#### Power

Inrush power absorbed	10.7 VA
-----------------------	---------

Operating consumption	2.9 VA
-----------------------	--------

Total power loss under IN	4 W
---------------------------	-----

Power loss per contact	1.5 W
------------------------	-------

Power dissipation per coil	1 W
----------------------------	-----

Contact rating with 230 V in AC7 category A	4.6 kW
---	--------

Contact rating with 230 V in AC7 category B	880 W
---	-------

#### Tripping

Time of response when opening	15 ms
-------------------------------	-------

Time of response when closing	25 ms
-------------------------------	-------

**Endurance**

Electric endurance in number of cycles	30000
Number of mechanical operations	100000

**Fluorescent bulbs control**

Max. power with fluorescent parallel lamps	810 VA
Fluorescent lamps in duo circuit	1990 VA
Max. load fluorescent lamp	950 VA

**Incandescent bulbs control**

Max. power with incandescent lamps	1900 W
------------------------------------	--------

**Installation, mounting**

Tightening torque	1,2Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 10mm <sup>2</sup>
Type of contacts	2NO
Connection cross-section of the control cable solid	1 / 10 mm <sup>2</sup>

**Equipment**

Can be accessorized	Yes
---------------------	-----

**Use**

Local operation/hand operation	Yes
--------------------------------	-----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C