



HA305

## Load break switch 3P 100A

### Technical properties

#### Architecture

Type of order	Short thumb-grip
Number of poles	3 P
Type of case	Fixed built-in

#### Functions

Reversing switch	No
------------------	----

#### Configuration

Number of modules	6
-------------------	---

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

#### Electric current

Rated operational current in AC21 category B	100 A
Acceptable current rating with AC22 category A	100 A
Cut off current	10 kA
Rated current	100 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	2.5 kA
Rated operational current in AC21 category A	100 A
Acceptable current rating with AC22 category B	100 A
Rated operational current in AC23 category A	63 A
Acceptable current rating with AC23 category B	63 A

#### Dimensions

Width of installed product	108 mm
----------------------------	--------

**Power**

Total power loss under IN	9.3 W
Power loss per pole at In	3.1 W
Contact rating with 400 V in AC1	65 kW

**Cover, door**

Interlockable	Yes
---------------	-----

**Installation, mounting**

Tightening torque	6 - 6.6 Nm
Fixation type	DIN rail mounting or back plate mounting

**Connection**

Connection cross-sect. rigid cable	50mm <sup>2</sup> max.
------------------------------------	------------------------

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-20...70 °C
-----------------------	-------------