



HCA125Z

## Load Break Switch Disconnecter h3 x160 3P 125A CTC

### Technical properties

#### Architecture

Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

#### Functions

Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	Yes
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	SWITCH
Concurrently switching N-neutral	No

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV

#### Electric current

Rated current	125 A
Rated operational current in AC21	125 A

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Cover, door

Interlockable	Yes
---------------	-----

#### Materials

Toggle colour	Grey
---------------	------

#### Installation, mounting

Tightening torque	6Nm
-------------------	-----

Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes
<b>Connection</b>	
Type of connection	with screw
<b>Cable</b>	
Cable Material	Cu
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
<b>Use</b>	
Vibrations and shocks withstand	IEC 68068-2-52 Test FC
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Altitude	2000 m