



HA362

Load break switch 3P 1250A

Technical properties

Architecture

| | |
|-----------------|----------------|
| Number of poles | 3 P |
| Type of pole | 3 P |
| Type of case | Fixed built-in |

Functions

| | |
|------------------|----|
| Reversing switch | No |
|------------------|----|

Controls and indicators

| | |
|------------------------|----|
| Motor drive integrated | No |
|------------------------|----|

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 380 / 415 V |
|------------------------------|-------------|

Voltage

| | |
|---------------------------------|---------|
| Rated insulation voltage | 1000 V |
| Rated impulse withstand voltage | 12000 V |

Electric current

| | |
|--|--------|
| Rated operational current in AC21category B | 1250 A |
| Acceptable current rating with AC22 category A | 1250 A |
| Rated current | 1250 A |
| Short-circuit current with gI-gG fuses | 50 kA |
| Rated short-time withstand current 1s | 50 kA |
| Thermal rated current outside of housings | 1250 A |
| Rated operational current in AC21 category A | 1250 A |
| Acceptable current rating with AC22 category B | 1250 A |
| Rated operational current in AC23 category A | 1000 A |
| Acceptable current rating with AC23 category B | 1000 A |
| Conventional thermal current under enclosure at 40°C | 1250 A |

Power

| | |
|-------------------------------------|--------|
| Nominal power under 660 V, 50 Hz | 400 kW |
| Active power under 380/415 V, 50 Hz | 560 kW |
| Total power loss under IN | 255 W |
| Power loss per pole at In | 85 W |

Endurance

| | |
|---------------------------------|------|
| Number of mechanical operations | 4000 |
|---------------------------------|------|

Cover, door

| | |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

Installation, mounting

| | |
|---------------|---------------------|
| Fixation type | Back plate mounting |
|---------------|---------------------|

Connection

| | |
|--------------------|----------|
| Type of connection | Terminal |
|--------------------|----------|

Equipment

| | |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
|---|---|

| | |
|---|---|
| Number of auxiliary contacts as normally open contact | 0 |
|---|---|

| | |
|---|---|
| Number of auxiliary contacts as change-over contact | 0 |
|---|---|

| | |
|---|---------------------|
| Width available for insulation connection | 185 mm ² |
|---|---------------------|

| | |
|----------------------|----|
| Motor drive optional | No |
|----------------------|----|

Standards

| | |
|---------------|-------------|
| Standard text | IEC 60947-3 |
|---------------|-------------|

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP00 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20...70 °C |
|-----------------------|-------------|