



HHA030Z

**Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 32A 25kA CTC**

**Technical properties**

**Architecture**

Neutral position	without neutral
Number of protected poles	1
Number of poles	1 P

**Functions**

Trip Unit	TM F/F
Integrated earth fault protection	No
Concurrently switching N-neutral	No

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage Ue	220 / 240 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	32 A
Thermal protection nob setting xIN	1
Rating current 10°C according to IEC 60947	43.8 A
Rating current 15°C according to IEC 60947	42.5 A
Rating current 20°C according to IEC 60947	41.2 A
Rating current 25°C according to IEC 60947	39.8 A
Rating current 30°C according to IEC 60947	38.4 A
Rating current 35°C according to IEC 60947	36.9 A
Rating current 40°C according to IEC 60947	35.3 A
Rating current 45°C according to IEC 60947	33.7 A
Rating current 50°C according to IEC 60947	32 A
Rating current 55°C according to IEC 60947	30.1 A
Rating current 60°C according to IEC 60947	28.2 A
Rating current 65°C according to IEC 60947	26.1 A
Rating current 70°C according to IEC 60947	23.9 A

Breaking capacity on 1 pole for IT 230V NF 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	25 kA
Range of the thermal adjustment	32 A
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	25 kA
<b>Dimensions</b>	
Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	25 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Total power loss under IN	3 W
Power loss per pole at In	3 W
<b>Endurance</b>	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
<b>Installation, mounting</b>	
Tightening torque	6Nm
<b>Connection</b>	
Connection cross-sect. rigid cable	6 / 95mm <sup>2</sup>
<b>Cable</b>	
Cable Material	Cu
<b>Settings</b>	
Range of the magnetic adjustment	600 A
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes
<b>Use cases</b>	
Category of use	A
<b>Standards</b>	
Standard text	IEC 60947-2
European directive WEEE	concerned

**Use conditions**

---

Degree of pollution according to IEC 60664 /  
IEC 60947-23

---

Altitude

2000 m

**temperatur**

---

Temperature of calibration

50 °C