



HIB420M

**Motorized transfer switch 4P 200A**

**Technical properties**

**Architecture**

Type of order	Not applicable
Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

**Functions**

Reversing switch	Yes
------------------	-----

**Controls and indicators**

Motor drive integrated	Yes
------------------------	-----

**Main electrical features**

Rated operational voltage Ue	380 / 690 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

**Electric current**

Rated operational current in AC21category B	200 A
Acceptable current rating with AC22 category A	200 A
Rated current	200 A
Short-circuit current with gl-gG fuses	50 kA
Rated short-time withstand current 1s	7 kA
Rating current 10°C according to IEC 60947	200 A
Rating current 15°C according to IEC 60947	200 A
Rating current 20°C according to IEC 60947	200 A
Rating current 25°C according to IEC 60947	200 A
Rating current 30°C according to IEC 60947	200 A
Rating current 35°C according to IEC 60947	200 A
Rating current 40°C according to IEC 60947	200 A
Rating current 45°C according to IEC 60947	180 A
Rating current 5°C according to IEC 60947	200 A
Rating current 50°C according to IEC 60947	180 A
Rating current 55°C according to IEC 60947	160 A
Rating current 60°C according to IEC 60947	160 A

Rating current 65°C according to IEC 60947	140 A
Rating current 70°C according to IEC 60947	140 A
Rated operational current in AC21 category A	200 A
Acceptable current rating with AC22 category B	200 A
Rated operational current in AC23 category A	200 A
Acceptable current rating with AC23 category B	200 A
Conventional thermal current under enclosure at 40°C	200 A
<b>Power</b>	
Total power loss under I <sub>N</sub>	16.4 W
Power loss per pole at I <sub>n</sub>	4.1 W
Contact rating with 400 V in AC1	131 kW
<b>Cover, door</b>	
Interlockable	Yes
<b>Installation, mounting</b>	
Tightening torque	20 - 22 Nm
<b>Connection</b>	
Type of connection	Terminal
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	1
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
<b>Standards</b>	
Standard text	IEC 60947-3 ; IEC 60947-6
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Altitude	2000 m
Storage/transport temperature	-40...70 °C