



HR502

**Earth Leakage Relay 0.3A instantaneous Trip Type A**

**Technical properties**

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 V
------------------------------	-------

**Voltage**

Max operating voltage	276 V
-----------------------	-------

**Electric current**

Rated residual operating current	300 mA
----------------------------------	--------

Torroïds : Allowed overload	30kA / 100ms
-----------------------------	--------------

**Power**

Power consumed	3 VA
----------------	------

**Installation, mounting**

Tightening torque	1,7Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 2,5mm <sup>2</sup>
---	------------------------

Connection cross-sect. rigid cable	1,5 / 4mm <sup>2</sup>
------------------------------------	------------------------

Connection cross-section in flexible cable for the measurement	1 / 2.5 mm <sup>2</sup>
--	-------------------------

Connection cross-section in massive cable for the measurement	1.5 / 4 mm <sup>2</sup>
---	-------------------------

**Settings**

Time delay of residual current	0 s
--------------------------------	-----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP30
---------------------	------

Residual current type	A
-----------------------	---

**Use conditions**

Operating temperature	-10...55 °C
-----------------------	-------------

Altitude	2000 m
----------	--------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------