



HXA001H



**Shunt trip 24V DC (x160-P160-x250-P250-x630-P630)**

**Technical properties**

**Voltage**

|                    |      |
|--------------------|------|
| DC control voltage | 24 V |
| Command voltage AC | 0 V  |

**Power**

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 0.7 W |
|---------------------------|-------|

**Equipment**

|   |   |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |
| Number of auxiliary contacts as change-over contact     | 0 |

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP4X |
|---------------------|------|

**Use conditions**

|  |        |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3      |
| Altitude   | 2000 m |