



JG320IN

**IP66 20A 3P ISOLATOR**

**Technical properties**

**Architecture**

Type of order	Short thumb-grip
Number of poles	3 P
Type of pole	3 P
Type of case	in housing

**Functions**

Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	Yes
Version as maintenance-/service switch	Yes

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage Ue	380 / 440 V
------------------------------	-------------

**Voltage**

Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V

**Electric current**

Acceptable current rating with AC22 category A	20 A
Rated current	20 A
Rated short-time withstand current Icw	240 A
Rated short-time withstand current Icw t=1s 380-415 V AC according IEC 60947-3	240 A
Rated operational current in AC21 category A	20 A
Rated operational current in AC21	20 A
Rated operational current in AC23 category A	20 A

**Dimensions**

Depth of installed product	87 mm
Height of installed product	170 mm
Width of installed product	84 mm

**Frequency**

**Cover, door**

---

Interlockable	Yes
---------------	-----

**Materials**

---

Toggle colour	Grey
---------------	------

**Installation, mounting**

---

Tightening torque	2Nm
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes

**Connection**

---

Connection cross-sect. rigid cable	2.5 / 4 mm <sup>2</sup>
Type of connection	with screw

**Equipment**

---

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No

**Standards**

---

Standard text	IEC 60947-3
---------------	-------------

**Safety**

---

Protection index IP	IP66
REACH conform	Yes
RoHS conform	Yes