



Insulated busbar 1P 63A prong 10mm² blue 18M

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole | 1 P |

Configuration

| | |
|-------------------|----|
| Number of modules | 13 |
|-------------------|----|

Compatibility

| | |
|--|-----------------|
| Intended for the compatible references | Modular devices |
|--|-----------------|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 415 V |
|------------------------------|-------|

Voltage

| | |
|---------------------------------|-------|
| Max operating voltage | 230 V |
| Rated impulse withstand voltage | 4 kV |

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Dimensions

| | |
|-----------------------------------|---------|
| Length | 228 mm |
| Pitch | 17.8 mm |
| Fixation distance in module steps | 1 |

Power supply

| | |
|---------------------------------------|---------|
| Number of phases for the power supply | 1 phase |
|---------------------------------------|---------|

Installation, mounting

| | |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

Connection

| | |
|--|----|
| Suitable for product with neutral busbar | No |
|--|----|

Equipment

| | |
|----------------------------------|----|
| Number of appliances to build in | 13 |
|----------------------------------|----|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

| | |
|-----------|-----|
| Insulated | Yes |
|-----------|-----|

KB163NG