



KDN280A

Insulated busbar 2P 80A fork 16mm² 12M

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 2 P |
| Type of pole | 2 P |

Main electrical features

| | |
|--|-------------|
| Rated operational voltage U _e | 230 / 400 V |
|--|-------------|

Voltage

| | |
|-----------------------|-------|
| Max operating voltage | 400 V |
|-----------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 80 A |
|---------------|------|

Dimensions

| | |
|--------|---------|
| Length | 210 mm |
| Pitch | 17.8 mm |

Materials

| | |
|--------|------------|
| Colour | stone grey |
|--------|------------|

Installation, mounting

| | |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

Connection

| | |
|--|-------------------|
| Connection cross-sect. rigid cable | 16mm ² |
| Suitable for product with neutral busbar | Yes |

Equipment

| | |
|----------------------------------|---|
| Number of appliances to build in | 6 |
|----------------------------------|---|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

| | |
|-----------|-----|
| Insulated | Yes |
|-----------|-----|