



HTG911H

Power supply 24V DC 2,5A at 70°C

Technical properties

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	196 / 264 V
Type of supply voltage	AC

Voltage

Output voltage	24 V DC
Rated operational voltage in DC	0 V

Electric current

Output intensity	2.5 A
Output intensity	2.5 A

Dimensions

Depth of installed product	63 mm
Height of installed product	93 mm
Installation height	0 m
Width of installed product	71 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Power absorbed	60 W
Total power loss under IN	6 W

Installation, mounting

Suitable for busbar mounting	No
Suitable for front mounting	No

Connection

Connection cross-section of input and output with screws, for massive conductors	1 / 2.5 mm ²
Connection cross section of access and exit with screws, for flexible conductor	0.75 / 2.5 mm ²
Type of connection	Screw connection

Equipment

Short-circuit protected	Yes
-------------------------	-----

Standards

European directive RoHs	compliant
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...70 °C
Storage/transport temperature	-40...85 °C