



MDN106P

## MCB 1P 6kA D-6A 1M

### Technical properties

#### Electric current

Rated current	6 A
Rated short-circuit breaking capacity $I_{cn}$ under 230 V AC according to IEC 60898-1	6 kA
Rated current -15°C	7,26 A
Rated current -10°C	7,13 A
Rated current -5°C	7 A
Rated current at 0°C	6,87 A
Rated current 5°C	6,73 A
Rated current 10°C	6,59 A
Rated current 15°C	6,45 A
Rated current at 20°C	6,30 A
Rated current 25°C	6,15 A
Rated current 30°C	6 A
Rated current 35°C	5,84 A
Rated current at 40°C	5,68 A
Rated current at 45°C	5,52 A
Rated current at 50°C	5,35 A
Rated current 55°C	5,17 A
Rated current 60°C	4,99 A
Rated current 65°C	4,80 A
Rated current 70°C	4,60 A

#### Architecture

Type of pole	1P
Curve	D

#### Capacity

Number of modules	1
-------------------	---

#### Main electrical attributes

Rated short-circuit breaking capacity $I_{cn}$ AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2,80-2,80 Nm
Nominal tightening torque down terminal	2,80-2,80 Nm

#### Voltage

Rated operational voltage $U_e$	240 - 415 V
Type voltage supply	AC
Rated insulation voltage $U_i$	500 V

**Frequency**

Frequency	50-60 Hz
-----------	----------

**Connection**

Cross-section of input and output with screws, for massive conductors	1-35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1-25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1-25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1-35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2,80 - 2,80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Air humidity protection	95%/55°C
Operating temperature	-25-70 °C

**Power**

Total power loss under IN	1,31 W
---------------------------	--------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	84,60 mm
Width	17,70 mm
Depth	70 mm