



HZI811

Controller

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	6
-------------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	58 mm
Height of installed product	93 mm
Width of installed product	106 mm

Power

Power consumed	7.5 VA
----------------	--------

Measurement

Frequency measuring range	50 to 60 Hz
Voltage measurement range	110 to 400 V

Equipment

Type of display	LCD
-----------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2X
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-20...60 °C
Altitude	2000 m
Storage/transport temperature	-20...60 °C