



MSN306

## MCB 3P 6kA C-6A 3M

### Technical properties

#### Electric current

Rated current	6 A
Rated current -15°C	7,3 A
Rated current -10°C	7,1 A
Rated current -5°C	7 A
Rated current at 0°C	6,8 A
Rated current 5°C	6,7 A
Rated current 10°C	6,6 A
Rated current 15°C	6,4 A
Rated current at 20°C	6,3 A
Rated current 25°C	6,1 A
Rated current 30°C	6 A
Rated current 35°C	5,8 A
Rated current at 40°C	5,7 A
Rated current at 45°C	5,5 A
Rated current at 50°C	5,3 A
Rated current 55°C	5,1 A
Rated current 60°C	5 A
Rated current 65°C	4,8 A
Rated current 70°C	4,6 A

#### Architecture

Type of pole	3P
Curve	C

#### Capacity

Number of modules	3
-------------------	---

#### Installation, mounting

Nominal tightening torque top terminal	2,80 - 2,80 Nm
Nominal tightening torque down terminal	2,80 - 2,80 Nm
Nominal tightening torque	2,80 - 2,80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

#### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

<b>Voltage</b>	
Rated operational voltage Ue	415 - 415 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V
<b>Frequency</b>	
Frequency	50 - 60 Hz
<b>Connection</b>	
Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>
<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C
<b>Power</b>	
Total power loss under IN	3,8 W
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	83 mm
Width	52,50 mm
Depth	70 mm