




MZ201



Auxiliary contact 1C+1O 6A 240V AC

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage U_e	230 / 415 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	4000 V
Max operating voltage	240 V
Rated operational voltage in DC	12 / 250 V

Electric current

Acceptable current rating with AC1	6 A
Rated current	6 A
$I_{min}=f(U=12V\ DC)$ for power circuit	0.3 A
$I_{min} = f (U = 230\ V\ DC)$	0.6 A
$I_{min}=f(U=400V\ AC)$ for power circuit	3 A

Dimensions

Depth of installed product	40 mm
Height of installed product	80 mm
Width of installed product	9.5 mm

Power

Total power loss under I_N	0.1 W
------------------------------	-------

Endurance

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

Installation, mounting

Factory fitted	No
----------------	----

Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1
Quantity of INV contacts	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------