



NDN163A

**MCB 1P 10kA/15kA D-63A 1M**

**Technical properties**

**Electric current**

Rated current	63 A
Rated short-circuit breaking capacity $I_{cn}$ under 230 V AC according to IEC 60898-1	10 kA
Rated current -25°C	81,04 A
Rated current at -20°C	79,57 A
Rated current -15°C	78,07 A
Rated current -10°C	76,54 A
Rated current -5°C	75,05 A
Rated current at 0°C	73,54 A
Rated current 5°C	72,03 A
Rated current 10°C	70,52 A
Rated current 15°C	69 A
Rated current at 20°C	67,47 A
Rated current 25°C	65,95 A
Rated current 30°C	63 A
Rated current 35°C	62,03 A
Rated current at 40°C	60,50 A
Rated current at 45°C	58,68 A
Rated current at 50°C	58,27 A
Rated current 55°C	52,80 A
Rated current 60°C	50,51 A
Rated current 65°C	48,12 A
Rated current 70°C	45,60 A

**Architecture**

Type of pole	1P
Curve	D

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity $I_{cn}$ AC according to IEC 60898-1	10 kA
Nominal tightening torque top terminal	2,80 - 2,80 Nm
Nominal tightening torque down terminal	2,80 - 2,80 Nm

**Voltage**

Rated operational voltage $U_e$	230 - 400 V
---------------------------------	-------------

Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V
<b>Frequency</b>	
Frequency	50 - 60 Hz
<b>Connection</b>	
Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
<b>Installation, mounting</b>	
Nominal tightening torque	2,80 - 2,80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-25 - 70 °C
<b>Power</b>	
Total power loss under IN	5,73 W
<b>Endurance</b>	
Electric endurance in number of cycles	4000
Number of mechanical operations	20000
<b>Connectivity</b>	
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	83 mm
Width	17,50 mm
Depth	70 mm