




MZ204



Shunt trip 24-48V AC 12-48V DC

Technical properties

Power

Inrush power absorbed 27 VA

Use conditions

Operating temperature -25 - 60 °C

Voltage

Command voltage AC 24 - 48 V

Command voltage DC 12 - 48 V

Type voltage supply AC/DC

Rated insulation voltage U_i 4000 V

Dimensions

Height 83 mm

Width 18 mm

Depth 68 mm