




SK603



## Ammeter switch 3 O

### Technical properties

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

#### Controls and indicators

|                                   |   |
|-----------------------------------|---|
| Number of positions of the switch | 4 |
|-----------------------------------|---|

#### Main electrical features

|                              |       |
|------------------------------|-------|
| Rated operational voltage Ue | 660 V |
| Frequency                    | 50 Hz |

#### Voltage

|                          |       |
|--------------------------|-------|
| Rated insulation voltage | 690 V |
|--------------------------|-------|

#### Electric current

|               |      |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

#### Dimensions

|                             |       |
|-----------------------------|-------|
| Depth of installed product  | 64 mm |
| Height of installed product | 85 mm |
| Width of installed product  | 70 mm |

#### Power

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 1 W |
|---------------------------|-----|

#### Network configuration

|              |                         |
|--------------|-------------------------|
| Network type | tree-phase with neutral |
|--------------|-------------------------|

#### Installation, mounting

|               |          |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

#### Connection

|   |                         |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 1,5 / 10mm <sup>2</sup> |
| Connection cross-sect. rigid cable        | 1 / 6mm <sup>2</sup>    |
| Type of connection                        | with screw              |

#### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...40 °C |
| Storage/transport temperature | -40...80 °C |