



SPB165R

**Surge Protection Device 1P T2 TNC Uc 320V In 20kA I<sub>max</sub> 65kA remote contact**

**Technical properties**

**Configuration**

Number of modules	1
-------------------	---

**Controls and indicators**

Indicator lamp	Optic
----------------	-------

**Main electrical features**

Rated operational voltage U <sub>e</sub>	240 / 415 V
--	-------------

Frequency	50/60 Hz
-----------	----------

Nominal discharge current (I <sub>n</sub> ) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	20 kA
--	-------

**Voltage**

Maximum continuous operating voltage U <sub>c</sub>	320 V
---	-------

Voltage protection level U <sub>p</sub> according to IEC61643-1	1.45 kV
---	---------

Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC61643-11	1.7 kV
--	--------

Voltage level U <sub>p</sub> L-N/PEN IEC61643-11	1.45 kV
--	---------

**Electric current**

Calibration of the protection upstream	160 A
--	-------

Max discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	65 kA
--	-------

**Dimensions**

Depth of installed product	58.2 mm
----------------------------	---------

Height of installed product	89.8 mm
-----------------------------	---------

Width of installed product	17.7 mm
----------------------------	---------

**Electrical specifications**

Short-circuit breaking capacity (I <sub>sc</sub> cr)	25 kA
--	-------

Signal contact Cross-sections	0.14 / 1.5 mm <sup>2</sup>
-------------------------------	----------------------------

Signal contact Current carrying capacity AC/DC	3 / 1 A
--	---------

Signal contact Voltage rating AC/DC	250 / 30 V
-------------------------------------	------------

**Network configuration**

Network type	TN-C
--------------	------

**Installation, mounting**

Tightening torque	3
-------------------	---

**Connection**

Connection cross-section of input and output with screws, for massive conductors	1.5 / 35 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1.5 / 25 mm <sup>2</sup>
<b>Standards</b>	
Approvals	KEMA
Test class IEC61643-11 / VDE0675-6-11	T2
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-40...80 °C