



SPB408D

## Surge Protection Device 4P TNS/TT U<sub>c</sub> 275V I<sub>n</sub> 2 kA I<sub>max</sub> 8 kA U<sub>p</sub> 1kV

### Technical properties

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Rated operational voltage U <sub>e</sub>	240 / 415 V
Frequency	50/60 Hz
Nominal discharge current (I <sub>n</sub> ) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	2 / 20 kA

#### Voltage

Maximum continuous operating voltage U <sub>c</sub>	275 V
Voltage protection level U <sub>p</sub> according to IEC61643-1	0.9 kV
Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC61643-11	1.5 kV
Voltage level U <sub>p</sub> L-N/PEN IEC61643-11	0.9 kV

#### Electric current

Calibration of the protection upstream	125 A
Max discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	8 / 40 kA

#### Dimensions

Depth of installed product	58.2 mm
Height of installed product	89.8 mm
Width of installed product	71.2 mm

#### Electrical specifications

Short-circuit breaking capacity (I <sub>sc</sub> cr)	25 kA
--	-------

#### Network configuration

Network type	TT/TN-S
--------------	---------

#### Installation, mounting

Tightening torque	3
-------------------	---

#### Connection

Connection cross-section of input and output with screws, for massive conductors	1.5 / 35 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1.5 / 25 mm <sup>2</sup>

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

**Use conditions**

---

Operating temperature

-40...80 °C