



SK602



Voltmeter switch 3"o

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Controls and indicators

| | |
|-----------------------------------|---|
| Number of positions of the switch | 7 |
|-----------------------------------|---|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 660 V |
| Frequency | 50 Hz |

Voltage

| | |
|--------------------------|-------|
| Rated insulation voltage | 690 V |
|--------------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 64 mm |
| Height of installed product | 85 mm |
| Width of installed product | 70 mm |

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 1 W |
|---------------------------|-----|

Network configuration

| | |
|--------------|-------------------------|
| Network type | tree-phase with neutral |
|--------------|-------------------------|

Installation, mounting

| | |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

Connection

| | |
|------------------------------------|----------------------|
| Connection cross-sect. rigid cable | 1 / 6mm ² |
| Type of connection | with screw |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...40 °C |
| Storage/transport temperature | -40...80 °C |