



ST315



Safety transformer 63VA 230V12-24V

Technical properties

Configuration

Number of modules	6
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4000 V
Output voltage 2	24 V
Open circuit voltage secondary	14.2 / 26.5 V
Output voltage	12 / 24 V

Electric current

Output intensity 2	2.63 A
Output intensity	5.25 A

Dimensions

Depth of installed product	68 mm
Height of installed product	85 mm
Width of installed product	105 mm

Power

Power consumed	63 VA
----------------	-------

Power supply

Transformer	Safety transformer to
-------------	-----------------------

Installation, mounting

Tightening torque	1,2Nm
Suitable for surface mounting	Yes
Suitable for flush-mounting	No
Mounting type	din-Rail

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Cable

Max. cable length to door actuator release 0.5 A	max. 100 m
---	------------

Max. cable length to door actuator release 1
A

max. 50 m

Equipment

On/Off switch

No

Short-circuit protected

Yes

Standards

Standard text

EN 61558-2-6

Approvals

EN 61558-2-6

Safety

Temperature protection

Yes

Use conditions

Operating temperature

-20...35 °C

Altitude

<= 2000 m