



SPA412A

## SPD 4P monobloc 12.5kA class 1 with light indicator TT

### Technical properties

#### Capacity

Number of modules 8

#### Voltage

Rated operational voltage  $U_e$  230 - 230 V

Continuous operating voltage  $U_c$  according to IEC 61643-1 255 V

Voltage protection level  $U_p$  according to IEC 61643-1 2,50 kV

#### Electric current

Nominal discharge current  $I_n$  8 - 20  $\mu$ s L-N(PEN)/N-PE IEC 61643 12.5 kA

Max. overcurrent protection device, parallel connection (fuse) 315 A

Max. discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 50 kA

#### Dimensions

Height 90 mm

Width 144 mm

Depth 68 mm

#### Use conditions

Operating temperature -40 - 60 °C

#### Network configuration

Network type TT, TN

#### Equipment

With remote signalling contact No

#### Standards

Requirement class IEC 61643 T1

#### Frequency

Frequency 50 - 60 Hz

#### Installation, mounting

Nominal tightening torque 3,60 - 3,60 Nm