



TE370

IP20

3Ph Kwhmeter via CT with KNX output

Technical properties

Architecture

Bus system	KNX
------------	-----

Controls and indicators

Indication / display	LC display with illumination
Manual selection switches / push-buttons	with a manual operation button for scrolling through the values

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Electric current

Bus current consumption (data transfer)	8 mA
Making current	10 mA
Reference current	5 A
Max. measurement circuit current	5 A

Dimensions

Width of rail mounted device (RMD)	4 modules
------------------------------------	-----------

Power

Power consumption measuring element	per phase max. 2.8 VA
Total power loss under IN	2 W

Measurement

Idle power measurement	YES
------------------------	-----

Connection

Conductor cross-section (flexible)	1...6 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...10 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes	system
-------------------------------	--------

Equipment

Type of counter	other
-----------------	-------

<b>Use</b>	
Differentiation characteristic 2 - Sales	with display
Differentiation characteristic 3 - Sales	with integral bus coupling unit
<b>Standards</b>	
PTB certified product	1
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-10...55 °C
Storage/transport temperature	-25...70 °C
<b>Identification</b>	
Main design line	KNX