



TRM600AU



### Additional Control for latching relay or timer

#### Technical properties

##### Architecture

Fixing mode flush-mounting

##### Functions

Function reset function (to factory setting)

##### Configuration

Number of modules 0

##### Controls and indicators

Button / push-button with configuration and function button

##### Connectivity

Radio protocol KNX Radio

Receiver category 2

##### Main electrical features

Frequency 50/60 Hz

##### Electric current

Number of entry circuits 2

Maximum through current 500 mA~

##### Dimensions

Height of installed product 40 mm

Dimensions (LLxwxh) 40x40x18

Diameter 53 mm

Height 18 mm

##### Frequency

Transmission frequency 433 MHz

Radio reception frequency 433 MHz

Radio transmission/reception frequency 433.4 MHz

##### Power

Total power loss under IN 150 mW

Power dissipation per coil 100 mW

Radio transmission power 10 mW

##### Materials

Colour independent of design lines light grey

**LED control**

Max number of LED/CFL lamps	0
LED	with configuration and function LEDs

**Connection**

Conductor cross-section (flexible)	0.5...1.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.5...2.5 mm <sup>2</sup>
Type of connection	with screw-in lift terminals
Type of connection	with screw

**Settings**

Supported configuration modes	PB
Programming	toolless quicklink configuration using buttons and LED display

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Equipment**

Number of outputs	1
Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Modular expandability	No

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-15...45 °C
Storage/transport temperature	-25...70 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

**Identification**

Main design line	Electronics platform
------------------	----------------------