



SRA02005

## Bar/Cable-through Current Transformer BG 113 200/5A 2,5VA Class 1

### Technical properties

#### Architecture

Type of product	plug-in current transformer
-----------------	-----------------------------

#### Functions

Precision class	1
-----------------	---

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Rated insulation voltage	3 kV
--------------------------	------

#### Electric current

Maximum current of primary	200 A
Maximum current of secondary	5 A
Primary current	200 A

#### Dimensions

Depth of installed product	30 mm
Height of installed product	70 mm
Width of installed product	49.5 mm
width of opening	29.5 mm
Height of opening	20 mm

#### Power

Total power loss under IN	2.2 W
---------------------------	-------

#### Connection

Type of connection	screw
--------------------	-------

#### Accessories included

With copper rail	No
------------------	----

#### Equipment

Number of inputs	1
With shock protection	Yes

#### Standards

Certified product	no
European directive WEEE	concerned

#### Safety

Protection index IP	IP10
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-40...40 °C
Storage/transport temperature	-40...40 °C