



TYA661AN



**Dimmer 1 channel 300W**

**Technical properties**

**Functions**

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors
Function	Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus
Soft startup	bulb-preserving soft startup

**Configuration**

Number of modules	4
-------------------	---

**Controls and indicators**

With LED indication	Yes
Indicator lamp	yes
Operation	manual operation also possible without bus, e.g. on building site ; Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; Manual operation per channel via button with integrated status LED, thereby lockout of KNX function
Indication / display	status LED integrated in the manual operation button
Manual selection switches / push-buttons	selection switch for manual/bus operation as well as load setting
Button / push-button	with illuminated programming button

**Main electrical features**

Frequency	50/60 Hz
Rated current	4 mA

**Voltage**

Auxiliary voltage	230 V AC
Input voltage	230 V AC
Operating voltage over bus	21...32 V DC

**Electric current**

Bus current consumption (data transfer)	< 2.3 mA
---	----------

**Fuse**

Fuse	short-circuit proof and overload proof (display using LEDs) ; overheating protection (display using LEDs)
------	---

**Dimensions**

Width of rail mounted device (RMD)	4 modules
------------------------------------	-----------

<b>Power</b>	
Dimmable conventional transformers	300 VA
Incandescent bulb power	300 W
Total power loss under IN	320 mW
Power dissipation per coil	180 mW
Electronic transformers	300 W

#### **Power supply**

Supply voltage	230 V AC
----------------	----------

#### **Fluorescent bulbs control**

Dimmable energy-saving lamps	60 W
Power lighting fluo lamps	60W

#### **LED control**

Max number of LED/CFL lamps	8
Dimmable LED lamps	60 W
Dimmable 230 V retrofit LED lamps	60 W
Power LED	60 W

LED	Status LED integrated in manual operation button ; Overheating protection, display using LEDs ; Overload protection, display via LED
-----	--

#### **Incandescent bulbs control**

230 V incandescent lamps and halogen lamps	300 W
--	-------

#### **Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of load	universal
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

#### **Settings**

Supported configuration modes	system
Parameterisation	parameter definable behaviour in the event of bus voltage failure/return

#### **Scope of delivery**

Bus connection included	Yes
-------------------------	-----

#### **Equipment**

Type of dimmer	dimming actuator
Modular expandability	No
Dimming principle	phase cut-on or cut-off according to load type, self-learning ; minimum/maximum dimming values per channel settable on device

low noise

very low noise

---

**Use**

---

Local operation/hand operation	Yes
--------------------------------	-----

---

**Safety**

---

REACH conform	No
---------------	----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	No
--------------	----

---

Protection	with overheating, overload and short-circuit protection
------------	---

---

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

---

**Identification**

---

Device family	TYA
---------------	-----

---

Main design line	KNX
------------------	-----