



VF218PT



Small distributor,golf,flush,2row,36M,IP40,MS-terminal,Australia,N+PE,white door

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	36
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Insertion depth	72 mm
-----------------	-------

Depth of wall niche	72 mm
---------------------	-------

Depth of installed product	97.5 mm
----------------------------	---------

Internal depth	97.5 mm
----------------	---------

Height of installed product	418 mm
-----------------------------	--------

Installation height	382 mm
---------------------	--------

Width of installed product	460 mm
----------------------------	--------

Width in division units	18
-------------------------	----

Built-in height	382 mm
-----------------	--------

Built-in width	426 mm
----------------	--------

Cover, door

Identification of protection index	40
------------------------------------	----

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	No
---------------------------	----

Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	plastic
----------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	2
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	2
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	0
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	Yes
---------------------	-----

Standards

GWT Glow wire test	850 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	07
-----------------------------------------------	----

Protection class	isol.class II
------------------	---------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------